

# Eaton PVML-7-UNV34

Catalog Number: PVML-7-UNV34

Eaton Crouse-Hinds series Champ Pro PVML LED fixture, Cool white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 127 lm/W, Die cast aluminum, No mounting module, Type V, 347-480 Vac, 61W

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series Champ Pro PVML LED light fixture	PVML-7-UNV34
	<b>UPC</b>
	662276906143
<b>Product Length/Depth</b>	<b>Product Height</b>
13 in	13.13 in
<b>Product Width</b>	<b>Product Weight</b>
12.75 in	20.8 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

IEC

### NEMA Rating

4X

### Ingress protection (IP) ratings

IP66

## Product specifications

### Lumens

7000

### Lumens per watt

127

### Color temperature

Cool white

### Mounting Method

No mounting module

### Optical distribution

Type V

### Guard type

No guard

### Voltage rating

347-480 Vac

### Frequency rating

50/60 Hz

### Wattage

61W

### Dimming

Dimmable driver

### Power factor

> 0.90

### Equivalent luminaire

175W HID

### Material

Die cast aluminum

### Lens material

Heat and impact resistant glass

## Resources

### 3D models

[SP3D Design Package - Champ Pro PVML Industrial LED Light](#)

[Fixtures](#)

[Brochures](#)

[Crouse-Hinds series industrial LED lighting solutions](#)

[Crouse-Hinds series Champ Pro PVML LED Luminaires - 3,000 to 13,000 lumens brochure](#)

[Crouse-Hinds series DLC approved lighting products](#)

[Crouse-Hinds series Global LED lighting portfolio](#)

### Catalogs

[Crouse-Hinds series Champ Pro PVML LED luminaires - 3,000 to 13,000 lumens catalog page](#)

### Certification reports

[Champ Pro PVML Industrial LED Light Fixtures Canadian certification](#)

[EC Declaration of Conformity - Crouse-Hinds series Champ Pro PVML LED Luminaires](#)

[Champ Pro PVML Industrial LED Light Fixtures UL certification](#)

### Installation instructions

[IF 1882 - Champ VMVL and PVML LED luminaires](#)

[IF 1888 - Champ VMVL and PVML Driver Replacement](#)

### Specifications and datasheets

[Eaton Specification Sheet - PVML-7-UNV34](#)

[Champ Pro PVM Industrial LED](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)