



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QCR1020 QCR Cable In Cable Out BKR 1P 20A 120/240VAC 10kai

Eaton Corp

Catalog Number	QCR1020
Manufacturer	Eaton Corp
Description	Eaton Quicklag Type QCR 1/2-Inch Industrial Thermal-Magnetic Circuit Breaker, Industrial Circuit Breaker, 20 A, 10 Kaic, Single-Pole, 120/240 V, Thermal-Magnetic, Cable-In/Cable-Out, QCR, Non-Interchangeable
Weight per unit	0.2000 (lbs/each)
Product Category	1 Pole Din Rail Mount Circuit

Features

connection	Cable-in/Cable-out
dimensions	4.7000 IN X 3.1000 IN X 1.2000 IN
interrupt rating	10
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	QCR CABLE IN CABLE OUT BKR 1P 20A 120/240VAC 10KAI
extra long description	ETN QCR1020 QCR 1P 20A 120/240V 10K
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton Quicklag Type QCR 1/2-inch Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCR, Non-interchangeable
Product Type	QCR 1P 20A 120/240V 10kaic

Manufacturer Information

Brand	Eaton
GTIN	00786679144060
Manufacturers Part Number	QCR1020
UPC	786679144060

Taxonomies, Classifications, and Categories

Category Description	Powerdefense Breakers
Type	Thermal magnetic circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional Energy Vessels and Equipment - Marine Vessels and Equipment - OtherOtherGeneration - Renewable Energy - Alternative EnergyDatacenters - IT Space: CI and Hyper Converged
standard	UL Listed,CSA Certified,HACR Rated