



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QBGFEP1030 Bolt On GFCB W/PCB 10KAIC 30A 30MA Trip

Eaton Corp

Catalog Number	QBGFEP1030
Manufacturer	Eaton Corp
Description	Eaton QB Gfci Circuit Breaker, Quicklag Industrial Ground Fault Thermal-Magnetic Circuit Breaker, Single-Pole, 30 Ma Trip Sensitivity, 30 A, 10 Kaic, 120V, Bolt-On Mounting
Weight per unit	0.4000 (lbs/each)
Product Category	On Circuit Breakers

Features

dimensions	5.1000 IN X 3.2000 IN X 1.3000 IN
interrupt rating	10
Poles	1
Voltage Rating	120V

Descriptions

Description	BOLT ON GFCB W/PCB 10KAIC 30A 30MA TRIP
extra long description	ETN QBGFEP1030 BOLT ON GFCB W/PCB 1
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton QB GFCI circuit breaker, Quicklag Industrial Ground Fault Thermal-Magnetic Circuit Breaker, Single-pole, 30 mA Trip Sensitivity, 30 A, 10 kAIC, 120V, Bolt-on mounting
Product Type	Bolt On GFCB W/PCB 10 Kaic 30A30MA Trip

Manufacturer Information

Brand	Eaton
GTIN	00786679145135
Manufacturers Part Number	QBGFEP1030
UPC	786679145135

Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	GFCI circuit breakers

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.4

Uses, Certifications, and Standards

Application	OtherMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper Converged
standard	UL 943