



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QBHW1015 1 Pole 15A QBHW BRKR

Eaton Corp

Catalog Number	QBHW1015
Manufacturer	Eaton Corp
Description	Eaton QB Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, 20 A, 22 Kaic, Single-Pole, 120/240 V, Non-Interchangeable, Q17, QBHW
Weight per unit	0.3000 (lbs/each)
Product Category	1 Pole Standard Trip Bolt-On

Features

dimensions	3.9000 IN X 1.2000 IN X 4.8000 IN
interrupt rating	22
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	1 POLE 15A QBHW BRKR
extra long description	ETN QBHW1015 QBHW BREAKER 1 POLE 15
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton QB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,20 A,22 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q17,QBHW
Product Type	QBHW Breaker 1 Pole 15a

Manufacturer Information

Brand	Eaton Corp
GTIN	00786679392003
Manufacturers Part Number	QBHW1015
UPC	786679392003

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

OtherGeneration - Conventional Energy - Conventional
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine
Vessels and Equipment - Marine Vessels and Equipment -
OtherGeneration - Renewable Energy - Alternative Energy

standard

UL Listed,CSA Certified