



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## QBHW2025 25A 2P 22KA B BKR

*Eaton Corp*

Catalog Number	QBHW2025
Manufacturer	Eaton Corp
Description	Eaton QB Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, 25 A, 22 Kaic, Two-Pole, 240 V, Non-Interchangeable, Q7, QBHW
Weight per unit	0.7000 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

### Features

dimensions	3.8000 IN X 2.3000 IN X 4.7000 IN
interrupt rating	22
Poles	2
Voltage Rating	120/240 V

### Descriptions

Description	25A 2P 22KA B BKR
extra long description	ETN QBHW2025 2P 25A QBHW 22KA 240V
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton QB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,25 A,22 kAIC,Two-pole,240 V,Non-Interchangeable,Q7,QBHW
Product Type	2P 25A QBHW 22KA 240V

### Manufacturer Information

Brand	Eaton
GTIN	00786679392607
Manufacturers Part Number	QBHW2025
UPC	786679392607

### Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

### Packaging

Carton	1
Weight Per each	0.7



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Other Datacenters - IT Space: CI and Hyper Converged Generation  
- Renewable Energy - Alternative Energy Generation -  
Conventional Energy - Conventional Energy Marine Vessels and  
Equipment - Marine Vessels and Equipment - Other

standard

CSA Certified, UL Listed