

Non-Plenum Electronic Wire

Overall Shield Electronic Wire

Part Number	Description	AWG	Cond	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
95211	22/2 stranded BC (7/30) OAS	22	2	CMR CL3R	10 lbs	0.129"	1,000' Box (46)	Gray (09)
95216	22/3 stranded BC (7/30) OAS	22	3	CMR CL3R	15 lbs	0.134"	1,000' Reel (06)	Gray (09)
67001	22/4 stranded BC (7/30) OAS	22	4	CMR CL3R	16 lbs	0.148"	500' Box (45) 1,000' Box (46)	Gray (09)
67005	22/6 stranded BC (7/30) OAS	22	6	CMR CL3R	23 lbs	0.178"	500' Box (45) 1,000' Box (46)	Gray (09)
67007	22/8 stranded BC (7/30) OAS	22	8	CMR CL3R	29 lbs	0.192"	500' Box (45) 1,000' Box (46)	Gray (09)
67009	22/12 stranded BC (7/30) OAS	22	12	CMR CL3R	41 lbs	0.230"	500' Box (45)	Gray (09)
95214	18/2 stranded BC (7/0.0152) OAS	18	2	CMR CL3R	18 lbs	0.163"	1,000' Reel (06) 1,000' Box (46)	Gray (09)
95218	18/3 stranded BC (7/0.0152) OAS	18	3	CMR CL3R	25 lbs	0.175"	1,000' Reel (06) 1,000' Box (46)	Gray (09)
67003	18/4 stranded BC (7/0.0152) OAS	18	4	CMR CL3R	34 lbs	0.193"	1,000' Reel (06) 1,000' Box (46)	Gray (09)
67006	18/6 stranded BC (7/0.0152) OAS	18	6	CMR CL3R	46 lbs	0.230"	1,000' Reel (06) 500' Box (45)	Gray (09)
67008	18/8 stranded BC (7/0.0152) OAS	18	8	CMR CL3R	59 lbs	0.249"	1,000' Reel (06)	Gray (09)
67010	18/12 stranded BC (7/0.0152) OAS	18	12	CMR CL3R	86 lbs	0.301"	1,000' Reel (06)	Gray (09)
95215	16/2 stranded BC (19/0.0117) OAS	16	2	CMR CL3R	26 lbs	0.187"	1,000' Reel (06)	Gray (09)
95219	16/3 stranded BC (19/0.0117) OAS	16	2	CMR CL3R	41 lbs	0.204"	1,000' Reel (06)	Gray (09)
95230	16/4 stranded BC (19/0.0117) OAS	16	4	CMR CL3R	46 lbs	0.218"	1,000' Reel (06)	Gray (09)
95253	14/2 stranded BC (19/0.0147) OAS	14	2	CMR CL3R	37 lbs	0.216"	1,000' Reel (06)	Gray (09)

95214

67003

95510

Each Pair Shielded Electronic Wire

Part Number	Description	AWG	Cond	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
95510	18/2pr stranded BC (7/0.0152) EPS	18	4 (2 pair)	CMR CL3R	40 lbs	0.302"	1,000' Reel (06)	Gray (09)

