

Specifications

Eaton R5A3025U

Eaton rotary disconnect switch, 25 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V

General specifications

PRODUCT NAME	Eaton rotary disconnect switch
CATALOG NUMBER	R5A3025U
UPC	786685402864
PRODUCT LENGTH/DEPTH	2.57 in
PRODUCT HEIGHT	3.35 in
PRODUCT WIDTH	1.77 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	CCC Marked
CERTIFICATIONS	CSA Certified UL 508 IEC Rated EN Listed
CATALOG NOTES	Suitable as motor disconnect

Physical Attributes

NUMBER OF POLES	Three-pole
SERIES	R5

Miscellaneous

PRODUCT CATEGORY	Rotary Switch
------------------	---------------

Performance Ratings

AMPERAGE RATING	25A
VOLTAGE RATING	600 V

Resources

CATALOGS	Commercial Distribution, Switching Devices, Volume 2, Tab 1
MULTIMEDIA	Switching Devices Flex Center
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - R5A3025U

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton R5A3025U

Eaton rotary disconnect switch, 25 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V

General specifications

PRODUCT NAME	Eaton rotary disconnect switch
CATALOG NUMBER	R5A3025U
UPC	786685402864
PRODUCT LENGTH/DEPTH	2.57 in
PRODUCT HEIGHT	3.35 in
PRODUCT WIDTH	1.77 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	CCC Marked
CERTIFICATIONS	CSA Certified UL 508 IEC Rated EN Listed
CATALOG NOTES	Suitable as motor disconnect

Physical Attributes

NUMBER OF POLES	Three-pole
SERIES	R5

Miscellaneous

PRODUCT CATEGORY	Rotary Switch
------------------	---------------

Performance Ratings

AMPERAGE RATING	25A
VOLTAGE RATING	600 V

Resources

CATALOGS	Commercial Distribution, Switching Devices, Volume 2, Tab 1
MULTIMEDIA	Switching Devices Flex Center
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - R5A3025U

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

