

Specifications



Photo is representative



Eaton R5A3040U

Eaton rotary disconnect switch, 40 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V

General specifications

PRODUCT NAME	Eaton rotary disconnect switch
CATALOG NUMBER	R5A3040U
UPC	786685402888
PRODUCT LENGTH/DEPTH	2.57 in
PRODUCT HEIGHT	3.35 in
PRODUCT WIDTH	1.77 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	CCC Marked
CERTIFICATIONS	CSA Certified EN Listed IEC Rated UL 508
CATALOG NOTES	Suitable as motor disconnect

Physical Attributes

NUMBER OF POLES Three-pole

SERIES R5

Miscellaneous

PRODUCT CATEGORY Rotary Switch

Performance Ratings

AMPERAGE RATING 40A

VOLTAGE RATING 600 V

Resources

CATALOGS [Commercial Distribution, Switching Devices, Volume 2, Tab 1](#)

MULTIMEDIA [Switching Devices Flex Center](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - R5A3040U](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton R5A3040U

Eaton rotary disconnect switch, 40 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V

General specifications

PRODUCT NAME	Eaton rotary disconnect switch
CATALOG NUMBER	R5A3040U
UPC	786685402888
PRODUCT LENGTH/DEPTH	2.57 in
PRODUCT HEIGHT	3.35 in
PRODUCT WIDTH	1.77 in
PRODUCT WEIGHT	0.5 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	CCC Marked
CERTIFICATIONS	CSA Certified EN Listed IEC Rated UL 508
CATALOG NOTES	Suitable as motor disconnect

Physical Attributes

NUMBER OF POLES Three-pole

SERIES R5

Miscellaneous

PRODUCT CATEGORY Rotary Switch

Performance Ratings

AMPERAGE RATING 40A

VOLTAGE RATING 600 V

Resources

CATALOGS [Commercial Distribution, Switching Devices, Volume 2, Tab 1](#)

MULTIMEDIA [Switching Devices Flex Center](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - R5A3040U](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

