



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



R838N #8 Nylon Ring 3/8" Stud

Nsi Industries

| | |
|------------------|---|
| Catalog Number | R838N |
| Manufacturer | Nsi Industries |
| Description | 8 Awg Nylon Insulated Ring 3/8" Stud, 25 Per Pack |
| Weight per unit | 0.2300 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|---------------------|------------------|
| Material | Nylon Insulation |
| Number of Terminals | 1 |
| Terminal Size | 3/8 |
| Voltage Rating | 600 V |
| Wire Size | 8 AWG |

Material, Color, and Finish

| | |
|-------|-----|
| Color | Red |
|-------|-----|

Descriptions

| | |
|------------------------|---|
| Description | #8 NYLON RING 3/8" STUD |
| extra long description | NSI R8-38N #8 Nylon Ring 3/8" Stud, |
| Features | 8 AWG Nylon Insulated Ring 3/8" Stud, 25 Per Pack |
| Long Description | 8 AWG Nylon Insulated Ring 3/8" Stud, 25 Per Pack |
| Product Type | #8 Nylon Ring 3/8" Stud, 25 Per Pack |
| Special Features | Nylon Insulated Ring Terminal 8 AWG - 50 Pack |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381068774 |
| Manufacturers Part Number | R8-38N |
| UPC | 662381068774 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | TERMINALS |
| Type | Nylon Insulated Ring Terminal |

Availability

| | |
|-------------|----|
| minimum qty | 25 |
|-------------|----|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 25 |
| Weight Per each | 0.23 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------------|------------------------|
| Application | Wire Termination |
| environmental conditions | 105 C |
| standard | cULus |