



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RCD38TRBK Radiant SP/3WAY SW+15A TR Outlet BK

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | RCD38TRBK |
| Manufacturer | Pass & Seymour/Legrand |
| Description | 15A 120/125V Radiant Combination Single Pole/3-Way Switch and TR Recptacle, Black |
| Weight per unit | 0.2083 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------------|--------------------|
| actuator | Rocker switch |
| amperage rating | 15 |
| Contact Configuration | 15A |
| Contact Rating | 125 |
| media | Yes |
| Mounting Type | Box |
| Number of Gangs | 1.0 |
| Number of Switches | 1.0 |
| operating cycles | 50000 |
| Poles | 3-Way, Single Pole |
| Switch Type | Push |
| Voltage | 125.0 V |
| Voltage Rating | 125 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|------|--|
| Size | Depth 1.43" x Width 1.29" x Height 3.81" |
|------|--|

Descriptions

| | |
|------------------------|---|
| Description | RADIANT SP/3WAY SW+15A TR OUTLET BK |
| extra long description | P&S RCD38TRBK RADIANT SP/3WAY SW+15 |
| Features | Locator Light, Combination |
| Long Description | 15A 120/125V Radiant Combination Single Pole/3-Way Switch and TR Recptacle, Black |
| Product Type | Radiant SP/3WAY SW+15A TR Outlet BK |
| Special Features | The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007055023 |
| Manufacturers Part Number | RCD38TRBK |
| UPC | 785007055023 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | Switch, Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.2083 |

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Residential |
| environmental conditions | UL94 V2 |
| Mounting | BOX |
| Operating Temperature | Maximum continuous +115°C, minimum -40°C |
| standard | UL, CULUS, cULus, UL Listed |