



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RSLB316 1" 316SS LB Conduit Body

*Robroy/Stainless Steel*

|                  |                                                                                                                                                                                                                                                                                                                      |
|------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | RSLB316                                                                                                                                                                                                                                                                                                              |
| Manufacturer     | Robroy/Stainless Steel                                                                                                                                                                                                                                                                                               |
| Description      | Robroy Stainless Conduit Bodies Are Designed to Withstand Harsh Corrosive Environments. Conduit Bodies Are 316 Stainless Steel and Are Used to Change The Direction Of Conduit and Make Wiring Pulls and Connections. Traditional Conduit Bodies Come With A Stamped Stainless Cover and Nitrile or Neoprene Gasket. |
| Weight per unit  | 2.9 (lbs/each)                                                                                                                                                                                                                                                                                                       |
| Product Category | Conduit & Raceways                                                                                                                                                                                                                                                                                                   |

### Features

|                |       |
|----------------|-------|
| Overall Height | 3.829 |
| Overall Width  | 2.06  |

### Material, Color, and Finish

|        |                  |
|--------|------------------|
| Finish | Electro-polished |
|--------|------------------|

### Dimensions and Weight

|                |       |
|----------------|-------|
| Overall Length | 7.458 |
|----------------|-------|

### Descriptions

|                        |                                                                                                                                                                                                                                                                                                                      |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | 1" 316SS LB CONDUIT BODY                                                                                                                                                                                                                                                                                             |
| extra long description | ROB-R LB316 LB COND Body 1" 316                                                                                                                                                                                                                                                                                      |
| Long Description       | Robroy Stainless Conduit Bodies are designed to withstand harsh corrosive environments. Conduit bodies are 316 stainless steel and are used to change the direction of conduit and make wiring pulls and connections. Traditional conduit bodies come with a stamped stainless cover and nitrile or neoprene gasket. |
| Product Type           | LB Cond Body 1" 316                                                                                                                                                                                                                                                                                                  |

### Manufacturer Information

|                           |                  |
|---------------------------|------------------|
| Brand                     | Robroy Stainless |
| GTIN                      | 00784011919260   |
| Manufacturers Part Number | LB316            |
| UPC                       | 784011919260     |

### Taxonomies, Classifications, and Categories

|                      |                             |
|----------------------|-----------------------------|
| Category Description | Stainless Steel EMT Conduit |
| Type                 | Conduit Body Assemblies     |

### Trade Size

|            |   |
|------------|---|
| Trade Size | 1 |
|------------|---|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight          | 2.88 |
| Weight Per each | 2.88 |

## Uses, Certifications, and Standards

|          |                                                  |
|----------|--------------------------------------------------|
| standard | UL 514Bm E231035, CSA C22.2 No. 18.1-04, TYPE 4X |
|----------|--------------------------------------------------|