



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RSRE216H 3/4"-1/2" Reducing Bushing Stainless

Robroy/Stainless Steel

Catalog Number	RSRE216H
Manufacturer	Robroy/Stainless Steel
Description	Robroy Stainless Hygienic Reducing Bushings Reduce Conduit Hubs to A Smaller Size. They Are Made Of 316 Stainless Steel and Are Specially Designed For The Hygienic System and Are Provided With A Circular Conduit Entry Gasket Made Of Fda Approved Silicone At The Female Thread and An Extended Design On The Male Threads Allowing For A Sealed Connection.
Weight per unit	0.1500 (lbs/each)
Product Category	Boxes & Covers

Features

Material	316
outside diameter	1.12

Material, Color, and Finish

Finish	Brushed
--------	---------

Dimensions and Weight

Length	1.5
--------	-----

Descriptions

Description	3/4"-1/2" REDUCING BUSHING STAINLESS
extra long description	ROB-R RE216H HYG RDC BSHG 3/4"-1/2"
Long Description	Robroy Stainless Hygienic Reducing Bushings reduce conduit hubs to a smaller size. They are made of 316 stainless steel and are specially designed for the hygienic system and are provided with a circular conduit entry gasket made of FDA approved silicone at the female thread and an extended design on the male threads allowing for a sealed connection.
Product Type	Hyg RDC BSHG 3/4"-1/2" 316 W/Cond Ent GSKT

Manufacturer Information

Brand	Robroy Stainless
GTIN	00784011919840
Manufacturers Part Number	RE216H
UPC	784011919840

Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	Reducing Bushings

Trade Size

Trade Size	3/4
------------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight	0.15
Weight Per each	0.15

Uses, Certifications, and Standards

standard	UL 514B, E200413, CSA C22.2 No. 18.1-04, NSF/ANSI/3-A 14159-1, TYPE 4X, IP69/IP69K
----------	---