



# S9621

9.5BR30/LED/3000K/800L/120V/D  
9.5 watt; BR30 LED; 105° beam spread; 3000K; Medium base;  
120 volts; Dimmable

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9621

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape
S9621	DiTTO	045923096211	120	9.5	65W	0.91	BR30
Base	ANSI Base	Lamp Code	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
Medium	E26	9.5BR30/LED/3000K/800L/120V/D	Frosted	5 3/16"	3.75"	800	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3000	Warm White	80	105	12/6	Box	ENERGY STAR	Yes
UL or ETL Listed		UL Classification				Warranty	
Yes		cULus - Damp Location Rated				<a href="#">3 Year Limited</a>	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9621

9.5BR30/LED/3000K/800L/120V/D  
9.5 watt; BR30 LED; 105° beam spread; 3000K; Medium base;  
120 volts; Dimmable

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9621

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape
S9621	DiTTO	045923096211	120	9.5	65W	0.91	BR30
Base	ANSI Base	Lamp Code	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
Medium	E26	9.5BR30/LED/3000K/800L/120V/D	Frosted	5 3/16"	3.75"	800	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3000	Warm White	80	105	12/6	Box	ENERGY STAR	Yes
UL or ETL Listed		UL Classification				Warranty	
Yes		cULus - Damp Location Rated				<a href="#">3 Year Limited</a>	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

