



S5835

MH1000/BT56/U/4K
 1000 watt; Metal Halide HID; Mogul base; BT56; Clear; 65 CRI;
 4000K

Features

- Uniform light distribution
- Superior performance
- High Efficiency



S5835

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | ANSI Code | Lamp Code |
|-------------|---------------|---------------|---------------------|----------------|-------------|------------|------------------|
| S5835 | 045923058356 | 1000 | BT56 | Mogul | E39 | M47/E | MH1000/BT56/U/4K |
| Finish | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Color | Probe Start |
| Clear | 15.38" | 7.00" | 10000 | 105000 | 4000 | Cool White | Yes |
| Pack | Package Type | CRI | Burning Position | RoHS Compliant | | | |
| 6 | Box | 65 | Universal | Yes | | | |



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027





S5835

MH1000/BT56/U/4K
 1000 watt; Metal Halide HID; Mogul base; BT56; Clear; 65 CRI;
 4000K

Features

- Uniform light distribution
- Superior performance
- High Efficiency



S5835

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | ANSI Code | Lamp Code |
|-------------|---------------|---------------|---------------------|----------------|-------------|------------|------------------|
| S5835 | 045923058356 | 1000 | BT56 | Mogul | E39 | M47/E | MH1000/BT56/U/4K |
| Finish | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Color | Probe Start |
| Clear | 15.38" | 7.00" | 10000 | 105000 | 4000 | Cool White | Yes |
| Pack | Package Type | CRI | Burning Position | RoHS Compliant | | | |
| 6 | Box | 65 | Universal | Yes | | | |



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

