



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2501 S. Fort Hood St.
76542-2312, TX Killeen
Phone: 254-554-5958
Fax: 254-554-8423



SC30 3/0 Cu Butt Splice

Nsi Industries

Catalog Number	SC30
Manufacturer	Nsi Industries
Description	Standardbarrel TINNEDCOPPERSPLICE3/0 Awg Standard Barrel Tinned Coppersplices Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	0.0800 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Orange
Finish	Tin Plated

Dimensions and Weight

Size	L=1.75 - OD=.620 - ID=.490
------	----------------------------

Descriptions

Description	3/0 CU BUTT SPLICE
extra long description	NSI SC-3/0 3/0 AWG Copper Short Bar
Features	StandardBarrel TinnedCopperSplice3/0 AWG Standard Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	StandardBarrel TinnedCopperSplice3/0 AWG Standard Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	3/0 Awg Copper Short Barrel Splice - Orange
Special Features	3/0 AWG (STR) - CU Splice



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2501 S. Fort Hood St.
76542-2312, TX Killeen
Phone: 254-554-5958
Fax: 254-554-8423

Manufacturer Information

Brand	NSi
GTIN	00662381037084
Manufacturers Part Number	SC-3/0
UPC	662381037084

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - CU Splice

Packaging

Carton	1
Package	25
Weight Per each	0.08

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486
Temperature Rating	90 C