



PRODUCT INFORMATION

SATCO-HYGRADE CEE QUALIFYING PRODUCTS

Consortium for Energy Efficiency • www.cee1.org

T8 Fluorescents

Features

- Qualifies for CEE High-Performance & Reduced Wattage Commercial Lighting Systems Initiative
- Long life – 20-30,000 hours depending on hours per start & ballast
- Available in 3000K to 6500K
- Designed to pass Federal TCLP test**



High-Performance 4' T8 Lamps

Item Number	Lamp Description	Shape	Watts	CCT	Rated Life (hrs.)*		Initial Lumens	Mean Lumens	CRI	Lumen Maint.	Master Case
					IS	RS/PRS					
S8426	F32T8/830/HL/ENV	Linear	32	3000	24,000	24,000	3200	3050	85	0.95	30
S8427	F32T8/835/HL/ENV	Linear	32	3500	24,000	24,000	3200	3050	85	0.95	30
S8428	F32T8/841/HL/ENV	Linear	32	4100	24,000	24,000	3200	3050	85	0.95	30
S8429	F32T8/850/HL/ENV	Linear	32	5000	24,000	24,000	3200	3050	85	0.95	30
S8430	F32T8/865/HL/ENV	Linear	32	6500	24,000	24,000	3100	2954	85	0.95	30

Reduced Wattage 4' T8 Lamps

Item Number	Lamp Description	Shape	Watts	CCT	Rated Life (hrs.)*		Initial Lumens	Mean Lumens	CRI	Lumen Maint.	Master Case
					IS	RS/PRS					
S8422	F28T8/830/ES/ENV	Linear	28	3000	24,000	24,000	2725	2560	85	0.94	30
S8423	F28T8/835/ES/ENV	Linear	28	3500	24,000	24,000	2725	2560	85	0.94	30
S8424	F28T8/841/ES/ENV	Linear	28	4100	24,000	24,000	2725	2560	85	0.94	30
S8425	F28T8/850/ES/ENV	Linear	28	5000	24,000	24,000	2700	2500	85	0.93	30
S8438	F32/25WT8/830/ES/ENV	Linear	25	3000	24,000	24,000	2400	2280	85	0.95	30
S8439	F32/25WT8/835/ES/ENV	Linear	25	3500	24,000	24,000	2400	2280	85	0.95	30
S8440	F32/25WT8/841/ES/ENV	Linear	25	4100	24,000	24,000	2400	2280	85	0.95	30
S8441	F32/25WT8/850/ES/ENV	Linear	25	5000	24,000	24,000	2375	2256	85	0.95	30
S8442	F32/25WT8/865/ES/ENV	Linear	25	6500	24,000	24,000	2300	2185	85	0.95	30
S8471	FB28T8/830/ES/ENV/28W	U-Bend	28	3000	20,000	24,000	2600	2440	85	0.94	16
S8472	FB28T8/835/ES/ENV/28W	U-Bend	28	3500	20,000	24,000	2600	2440	85	0.94	16
S8473	FB28T8/841/ES/ENV/28W	U-Bend	28	4100	20,000	24,000	2600	2440	85	0.94	16

*Based on 3 hour duty cycle. **Regulations may vary. Check your local and state regulations.



National Toll-Free: 800.43.SATCO (800.437.2826) www.satco.com

Distribution Centers: New York, Florida, Texas, Washington, California, Puerto Rico

Corporate Offices: 110 Heartland Blvd., Brentwood, NY 11717 800.437.2826 631.243.2022 Fax 631.243.2027