



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## SE75PSCCR0 1/4" BLK Expn Sleeve, 100' Roll *Panduit Corporation*

Catalog Number	SE75PSCCR0
Manufacturer	Panduit Corporation
Description	Fray Resistant Braided Expandable Sleeving, .75" (19.1 MM) Diameter, Can Be Cut With A Pair Of Scissors and Provides Continuous Abrasion Resistance For Wires, Cables, and Tubing. The Lightweight, Durable Protection Is Flexible and The Open Weave Will Not Trap Heat or Humidity. Polyethylene Terephthalate. 100 FT (30.5 M) Reel. Color Black.
Weight per unit	1.5 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

Material	PET
media	Yes
Nominal Size	0.75

### Material, Color, and Finish

Color	Black
-------	-------

### Dimensions and Weight

Diameter	0.63 - 1.0
Length	100

### Descriptions

Description	1/4" BLK EXPN SLEEVE,100' ROLL
extra long description	PAN SE75PSC-CR0 Pan-Wrap™ SE75PSC-C
Long Description	Fray resistant braided expandable sleeving, .75" (19.1 mm) diameter, can be cut with a pair of scissors and provides continuous abrasion resistance for wires, cables, and tubing. The lightweight, durable protection is flexible and the open weave will not trap heat or humidity. Polyethylene Terephthalate. 100 ft (30.5 m) reel. Color Black.
Product Type	Pan-Wrap™ SE75PSC-CR0 Fray Resistant Sleeving, Black, Pet, 0

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983816491
Manufacturers Part Number	SE75PSC-CR0
UPC	074983816491

### Taxonomies, Classifications, and Categories

Type	Braided Expandable Sleeving
------	-----------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per roll	1.52

## Uses, Certifications, and Standards

Application	Provides Continuous Abrasion Protection for Wires, Cables, Hoses, and Tubing; Highly Flexible Open Weave will not Trap Heat or Humidity; Allows for Use with Irregular Shapes
standard	CSA Certified, Compliant with U.S. and European passenger rail standards, UL Recognized E116868; RoHS Compliant
Temperature Rating	257