

# Eaton SFDN100

Catalog Number: SFDN100

Eaton Circuit Breaker Enclosure, 15-100A, Series C, NEMA 1, EHD, FD, FDB, HFD, Surface



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton enclosed circuit breaker	SFDN100
<b>UPC</b>	<b>Product Length/Depth</b>
786679257159	19.5 in
<b>Product Height</b>	<b>Product Width</b>
6.75 in	14.1 in
<b>Product Weight</b>	<b>Warranty</b>
11.4 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed CSA Certified	With Knockouts

## Product specifications

### Type

Circuit Breaker Enclosure

### Amperage Rating

15-100A

### Circuit breaker type

EHD, FD, FDB, HFD

### Enclosure

NEMA 1

### Series

Series C

### Mounting Method

Surface mounting

## Resources

### Brochures

[Customized Solutions - Customized Service](#)

### Drawings

[SFDN100 Circuit Breaker Enclosure - Drawing](#)

### Specifications and datasheets

[Eaton Specification Sheet - SFDN100](#)

[Enclosed Circuit Breakers - Technical Data](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton SFDN100

Catalog Number: SFDN100

Eaton Circuit Breaker Enclosure, 15-100A, Series C, NEMA 1, EHD, FD, FDB, HFD, Surface



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton enclosed circuit breaker	SFDN100
<b>UPC</b>	<b>Product Length/Depth</b>
786679257159	19.5 in
<b>Product Height</b>	<b>Product Width</b>
6.75 in	14.1 in
<b>Product Weight</b>	<b>Warranty</b>
11.4 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed CSA Certified	With Knockouts

## Product specifications

### Type

Circuit Breaker Enclosure

### Amperage Rating

15-100A

### Circuit breaker type

EHD, FD, FDB, HFD

### Enclosure

NEMA 1

### Series

Series C

### Mounting Method

Surface mounting

## Resources

### Brochures

[Customized Solutions - Customized Service](#)

### Drawings

[SFDN100 Circuit Breaker Enclosure - Drawing](#)

### Specifications and datasheets

[Eaton Specification Sheet - SFDN100](#)

[Enclosed Circuit Breakers - Technical Data](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)