



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SF10PLA Slide Dimmer-0-10V , 120/277VAC, LT. AI

Eaton Wiring Devices

Catalog Number	SF10PLA
Manufacturer	Eaton Wiring Devices
Description	Eaton Dimmer, No Neutral Required, #14 -12 Awg, Flush, 120/277 Vac, Back and Side, Wire Leads, Maintained, Light Almond, 60 HZ, Led, Flourescent, Single-Pole, Three-Way, Single-Phase, Polycarbonate, 1200/1660W 736902
Weight per unit	0.2330 (lbs/each)
Product Category	Lighting Dimmers

Descriptions

Description	SLIDE DIMMER-0-10V , 120/277VAC, LT. AL
extra long description	EWD SF10P-LA Slide Dimmer-0-10V , 1
Features	Bring the right ambiance to the room and save energy at the same time. Lighting controls reduce the amount of electricity used by your lights by controlling power loads at the switch, which saves electricity, reduces utility bills and extends the life of the bulb. Eaton's lighting control dimmers are compatible with most common lighting loads, including LED, CFL, MLV, ELV and Fluorescent. Available in multiple styles and colors, you can select the perfect dimmer for every room in your home or commercial bu
Long Description	Eaton dimmer, No neutral required, #14 -12 AWG, Flush, 120/277 Vac, Back and side, Wire Leads, Maintained, Light almond, 60 Hz, LED, Flourescent, Single-pole, Three-way, Single-phase, Polycarbonate, 1200/1660W 736902
Product Type	Slide Dimmer-0-10V , 120/277VAC, LT. AI

Manufacturer Information

Brand	Eaton
GTIN	00032664736902
Manufacturers Part Number	SF10P-LA
UPC	032664736902

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	SLIDE DIMMER

Packaging

Carton	1
Weight Per each	0.233



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

standard

NOM,cULus Listed