



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SLDSL6069S1EMWR *Discontinued* 6" Led Surface Trim CCT Select J-B

Cooper Lighting Solutions

Catalog Number	SLDSL6069S1EMWR
Manufacturer	Cooper Lighting Solutions
Description	6" Surface Led Downlight, 600 Lumens, 90CRI Field Selectable, 120V, Phase Cut 5% Dimming Driver, Matte White Finish, Recyclable 4-Color Unit Carton
Weight per unit	1.6 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.071A at 277V
Lamp Type	LED
Number of Lamps	1
Socket Type	N/A
Voltage Rating	120V

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	*DISCONTINUED* 6" LED SURFACE TRIM CCT SELECT J-B
extra long description	CLS SLDSL6069S1EMWR 6" SLD, 600LM,
Long Description	6" Surface LED Downlight, 600 lumens, 90CRI Field selectable, 120V, phase cut 5% dimming driver, Matte White Finish, recyclable 4-color unit carton
Product Type	6" SLD, 600LM, 5CCT, 120V
Special Features	Ceiling mounting in compatible junction boxes, Lumens up to 1200

Manufacturer Information

Brand	HALO
GTIN	00080083153121
Manufacturers Part Number	SLDSL6069S1EMWR
UPC	080083153121

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	SDSL Downlight

Packaging

Carton	1
Weight Per each	1.6



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	lighting
Mounting	Surface Mount
standard	UL Certified - Damp Location;NEC;NFPA;EMI/RFI per FCC 47CFR Part 15 Class B;AIR-TITE (TM) Certified ASTM E283;IECC Compliant;Energy Star Certified;RoHS Compliant;TM21 standards;LM79/LM80 Compliant;Title 24 Compliant