



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SLDSL6069S1EMWR 6" Led Surface Trim CCT Select J-Box Mount Only

Cooper Lighting Solutions

Catalog Number	SLDSL6069S1EMWR
Manufacturer	Cooper Lighting Solutions
Description	6" Surface Led Downlight, 600 Lumens, 90CRI Field Selectable, 120V, Phase Cut 5% Dimming Driver, Matte White Finish, Recyclable 4-Color Unit Carton
Weight per unit	1.6 (lbs/each)
Product Category	Lighting

### Features

amperage rating	0.071A at 277V
Lamp Type	LED
Number of Lamps	1
Socket Type	N/A
Voltage Rating	120V

### Material, Color, and Finish

Style	(blank)
-------	---------

### Descriptions

Description	6" LED SURFACE TRIM CCT SELECT J-BOX MOUNT ONLY
extra long description	CLS SLDSL6069S1EMWR 6" SLD, 600LM,
Long Description	6" Surface LED Downlight, 600 lumens, 90CRI Field selectable, 120V, phase cut 5% dimming driver, Matte White Finish, recyclable 4-color unit carton
Product Type	6" SLD, 600LM, 5CCT, 120V
Special Features	Ceiling mounting in compatible junction boxes, Lumens up to 1200

### Manufacturer Information

Brand	HALO
GTIN	00080083153121
Manufacturers Part Number	SLDSL6069S1EMWR
UPC	080083153121

### Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	SDSL Downlight

### Packaging

Carton	1
Weight Per each	1.6



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	lighting
Mounting	Surface Mount
standard	UL Certified - Damp Location;NEC;NFPA;EMI/RFI per FCC 47CFR Part 15 Class B;AIR-TITE (TM) Certified ASTM E283;IECC Compliant;Energy Star Certified;RoHS Compliant;TM21 standards;LM79/LM80 Compliant;Title 24 Compliant