

# Specifications

## Eaton SP1-240S

Eaton Surge Protection Device, SP1 series, 50 kAIC, 120/240V, 300 L-L, 150 L-N operating voltage, Split single-phase



### General specifications

<b>PRODUCT NAME</b>	Eaton SP1 surge protective device
<b>CATALOG NUMBER</b>	SP1-240S
<b>UPC</b>	786685448329
<b>PRODUCT LENGTH/DEPTH</b>	2.5 in
<b>PRODUCT HEIGHT</b>	4.8 in
<b>PRODUCT WIDTH</b>	2.9 in
<b>PRODUCT WEIGHT</b>	1.25 lb
<b>WARRANTY</b>	2 year
<b>CERTIFICATIONS</b>	UL 1449



Powering Business Worldwide

## Electrical properties

VOLTAGE RATING	120/240 V
PHASE	Split-phase

## Physical properties

TYPE	SP1
------	-----

## Resources

CATALOGS	<a href="#">Commercial Distribution, Switching Devices, Volume 2, Tab 1</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - SP1-240S</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton SP1-240S

Eaton Surge Protection Device, SP1 series, 50 kAIC, 120/240V, 300 L-L, 150 L-N operating voltage, Split single-phase



### General specifications

<b>PRODUCT NAME</b>	Eaton SP1 surge protective device
<b>CATALOG NUMBER</b>	SP1-240S
<b>UPC</b>	786685448329
<b>PRODUCT LENGTH/DEPTH</b>	2.5 in
<b>PRODUCT HEIGHT</b>	4.8 in
<b>PRODUCT WIDTH</b>	2.9 in
<b>PRODUCT WEIGHT</b>	1.25 lb
<b>WARRANTY</b>	2 year
<b>CERTIFICATIONS</b>	UL 1449

## Electrical properties

VOLTAGE RATING	120/240 V
PHASE	Split-phase

## Physical properties

TYPE	SP1
------	-----

## Resources

CATALOGS	<a href="#">Commercial Distribution, Switching Devices, Volume 2, Tab 1</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - SP1-240S</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

