



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SP331 Smooth Wallplate 3G Blank Box MT Iv

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | SP331 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Smooth Wall Plate 3-Gang Blank Box Mount |
| Weight per unit | 0.1707 (lbs/each) |
| Product Category | Wall Plates & Covers |

Features

| | |
|-----------------|-------------|
| cutout | Blank |
| indoor/outdoor | Indoor |
| insulation | Bare |
| Mounting Type | Box Mounted |
| Number of Gangs | 3 |
| orientation | Vertical |
| Wall Plate Type | Blank |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|-----------|------|
| Size | 5" |
| Thickness | 0.07 |

Descriptions

| | |
|------------------------|--|
| Construction | Plastic |
| Description | SMOOTH WALLPLATE 3G BLANK BOX MT IV |
| extra long description | P&S SP331 SMOOTH WALL PLATE 3G BLNK |
| Long Description | Smooth Wall Plate 3-Gang Blank Box Mount |
| Product Type | Smooth Wall Plate 3G BLNK Box MT Iv |
| Special Features | Non-combustible mar-proof material, seven standards colors, individually wrapped |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007186949 |
| Manufacturers Part Number | SP33-I |
| UPC | 785007186949 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | Wall Plate |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 15 |
| Package | 150 |
| Weight Per each | 0.1707 |

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | CSA, UL, CSA, UL514 |