



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SPJ8I Plastic Wallplate JR Jumbo 1G Duplex W/Out Line Iv

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | SPJ8I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Smooth Wall Plate, Junior-Jumbo 1-Gang Duplex |
| Weight per unit | 0.0743 (lbs/each) |
| Product Category | Wall Plates & Covers |

Features

| | |
|-----------------|----------------|
| cutout | Receptacle |
| insulation | Bare |
| media | Yes |
| Mounting Type | Exposed Screws |
| Number of Gangs | 1 |
| orientation | Vertical |
| Wall Plate Type | Outlet |

Dimensions and Weight

| | |
|-----------|------|
| Size | 7" |
| Thickness | 0.07 |

Descriptions

| | |
|------------------------|--|
| Description | PLASTIC WALLPLATE JR JUMBO 1G DUPLEX W/OUT LINE IV |
| extra long description | P&S SPJ8I PLST PLT JR JUMBO 1G DUPL |
| Long Description | Smooth Wall Plate, Junior-Jumbo 1-Gang Duplex |
| Product Type | PLST PLT JR Jumbo 1G Duplex W/O Lin I |
| Special Features | Non-combustible mar-proof material, seven standards colors, individually wrapped |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007680799 |
| Manufacturers Part Number | SPJ8-I |
| UPC | 785007680799 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | Wall Plate |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 200 |
| Weight Per each | 0.0743 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | CSA, UL, CSA, UL514 |