



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T1089 4" Alu T MK9 Conduit Body

Crouse-Hinds

Catalog Number	T1089
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Mark 9 Conduit Outlet Body, Copper-Free Aluminum, T Shape, 4"
Weight per unit	10.6 (lbs/each)
Product Category	Alum

Features

dimensions	18.7500 IN X 5.9400 IN X 8.1300 IN
Form	Form 5

Material, Color, and Finish

Finish	Hot Dip Galvanized
--------	--------------------

Dimensions and Weight

Height	2.60
Hub Size	1-1/4 in
Length	9.00
Width	2.75

Descriptions

Description	4" ALU T MK9 CONDUIT BODY
extra long description	CRS-H T1089 4 T MARK 9 CNDT OUTLET
Features	Mark 9 copper-free aluminum conduit bodies, covers and gaskets from Eaton's Crouse-Hinds Division are used in conduit systems to act as pull outlets for conductors being installed, provide openings for making splices and taps in conductors, make 90 degree bends in conduit runs, and provide for access to conductors for maintenance and future system changes. Mark 9 bodies are offered in seven different shapes, and they provide more room for heavier conductors.
Long Description	Eaton Crouse-Hinds series Condulet Mark 9 conduit outlet body, Copper-free aluminum, T shape, 4"
Product Type	4 T Mark 9 CNDT Outlet Body THRD Rigid
Special Features	Weight 332 Lb per 100

Manufacturer Information

Brand	Eaton
GTIN	00782274630007
Manufacturers Part Number	T1089
UPC	782274630007



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Form 9 condulets, covers & gaskets
Type	Conduit outlet body

Packaging

Carton	1
Weight Per each	10.6499

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Condulet
standard	UL 514B, CSA C22.2, CUL