

**Thermal**  
**T&B Catalog Number:**TA75DU32  
66201988568  
Active**UPC Number:****Status:****Description:**

3 pole thermal overload relay with 22-32 amp setting range

**Features**RESET button, manual and automatic selectable  
Test function and ON-OFF status indication  
Test function and ON-OFF status indication**Application**For use with single and three phase motors  
For use with single and three phase motors**General**

|                 |                                      |
|-----------------|--------------------------------------|
| Series          | TA75DU                               |
| Poles           | 3                                    |
| For Contactors  | A/E/F50-A/E/F75, A/E/F50N2-A/E/F75N3 |
| Output Contacts | 1 NC and 1 NO                        |
| Trip Class      | 10                                   |
| Reset Type      | Manual/Automatic                     |

**Dimension Information**

H x W x D (inches) 3.62 x 2.36 x 4.61

**Specifications**

Amp Setting Range (A) 22-32

**Packaging**

|                    |                 |
|--------------------|-----------------|
| Package in Units   | 1               |
| T&B Sold in UOM    | Each            |
| T&B Weight Per UOM | 80 lbs. per 100 |

**Certifications**

Approvals UL, CSA, CE

**For further technical assistance, please contact us...**Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.comT&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com

**Thermal**  
**T&B Catalog Number:**TA75DU32  
66201988568  
Active**UPC Number:****Status:****Description:**

3 pole thermal overload relay with 22-32 amp setting range

**Features**RESET button, manual and automatic selectable  
Test function and ON-OFF status indication  
Test function and ON-OFF status indication**Application**For use with single and three phase motors  
For use with single and three phase motors**General**

|                 |                                      |
|-----------------|--------------------------------------|
| Series          | TA75DU                               |
| Poles           | 3                                    |
| For Contactors  | A/E/F50-A/E/F75, A/E/F50N2-A/E/F75N3 |
| Output Contacts | 1 NC and 1 NO                        |
| Trip Class      | 10                                   |
| Reset Type      | Manual/Automatic                     |

**Dimension Information**

H x W x D (inches) 3.62 x 2.36 x 4.61

**Specifications**

Amp Setting Range (A) 22-32

**Packaging**

|                    |                 |
|--------------------|-----------------|
| Package in Units   | 1               |
| T&B Sold in UOM    | Each            |
| T&B Weight Per UOM | 80 lbs. per 100 |

**Certifications**

Approvals UL, CSA, CE

**For further technical assistance, please contact us...**Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.comT&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com