



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **TFX3LED40KMVOLT \*Delisted\*188W Led FLD 4K 25600L Trun 120-277V BRZ** *Lithonia Lighting - Acuity*

|                  |   |
|------------------|---|
| Catalog Number   | TFX3LED40KMVOLT   |
| Manufacturer     | Lithonia Lighting - Acuity  |
| Description      | The TFX3 Delivers 25, 600 Lumens and Can Replace Up to 400W Metal Halide. The TFX Led Floodlight Family Is An Industry-Leading Distributor Stock Solution Providing Cost-Effective and Energy-Efficient Solutions to Replace Hid Floodlights. In Addition, Payback Can Be Achieved In Less Than Two Years, Due to DLC Premium Listing and 140 Lumens Per Watt Efficacy. For The Full Solution, The TFX Comes In Four Sizes Delivering 7, 000 to 41, 000 Lumens Replacing 70W to 400W Metal Halide Luminaires. |
| Weight per unit  | 21.0 (lbs/each)   |
| Product Category | Led Floodlights   |

### Features

|                |              |
|----------------|--------------|
| average life   | 100,000      |
| Fixture Type   | FLOODLIGHT   |
| Hardware       | Yes          |
| Lamp Included  | Yes          |
| Lamp Type      | LED - Static |
| lumens         | 25,600 LM    |
| Material       | Aluminum     |
| Power Source   | Hardwired    |
| Shape          | Rectangular  |
| Voltage Rating | 120-277      |
| Wattage        | 188          |

### Material, Color, and Finish

|                             |             |
|-----------------------------|-------------|
| Color                       | Bronze      |
| color rendering index (cri) | 70          |
| color temperature           | 4000        |
| Finish                      | Gloss       |
| Lens Material               | Glass       |
| Style                       | Traditional |

### Dimensions and Weight

|        |             |
|--------|-------------|
| Height | 17.75       |
| Length | 5           |
| Size   | 18x18x17.75 |
| Width  | 18          |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | *DELISTED*188W LED FLD 4K 25600L TRUN 120-277V BRZ   |
| extra long description | LITH TFX3 LED 40K MVOLT YK DDBXD Ou  |
| Long Description       | The TFX3 delivers 25,600 lumens and can replace up to 400W metal halide. The TFX LED floodlight family is an industry-leading distributor stock solution providing cost-effective and energy-efficient solutions to replace HID floodlights. In addition, payback can be achieved in less than two years, due to DLC Premium listing and 140 lumens per watt efficacy. For the full solution, the TFX comes in four sizes delivering 7,000 to 41,000 lumens replacing 70W to 400W metal halide luminaires. |
| Product Type           | Floodlight   |

## Manufacturer Information

|                           |                             |
|---------------------------|-----------------------------|
| Brand                     | Lithonia Lighting           |
| GTIN                      | 00193047670258              |
| Manufacturers Part Number | TFX3 LED 40K MVOLT YK DDBXD |
| UPC                       | 193047670258                |

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING |
| Type                 | FLOODLIGHT  |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight          | 20.9 |
| Weight Per each | 21   |

## Uses, Certifications, and Standards

|                          |               |
|--------------------------|---------------|
| environmental conditions | OUTDOOR       |
| Mounting                 | YOKE          |
| standard                 | ULDLC Premium |