



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TM870NICC10 Radiant Switch 1P 15A 120/277V Ni

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | TM870NICC10 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | The Perfect Upgrade For Your Basic Light Switch, The Single-Pole Switch From The Radiant Registered Collection Provides On/Off Control Of A Light or Fixture From A Single Location, While Combining Clean Lines and Smooth Paddle Action For A Sophisticated Touch. Made Exclusively For Use With Screwless Wall Plates From The Radiant Registered Collection, Sold Separately. |
| Weight per unit | 0.1775 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|--------------------|---------------------|
| actuator | Rocker switch |
| amperage rating | 15 |
| Contact Rating | 15 Amp, 120/125 VAC |
| Material | Thermoplastic |
| media | Yes |
| Mounting Type | Box |
| Number of Gangs | 1.0 |
| Number of Switches | 1.0 |
| operating cycles | 50000 |
| Poles | 1 |
| Switch Type | Paddle |
| Voltage | 120/277 V |
| Voltage Rating | 120 |
| Wire Size | #14 - #10 Awg |

Material, Color, and Finish

| | |
|--------|----------|
| Finish | Metallic |
|--------|----------|

Dimensions and Weight

| | |
|------|--|
| Size | 1.27" Depth x 1.43" Width x 4.19" Height |
|------|--|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | RADIANT SWITCH 1P 15A 120/277V NI |
| extra long description | P&S TM870NICC10 RADIANT SWITCH 1P 1 |
| Features | The perfect upgrade for your basic light switch, the Single-Pole Switch from the radiant Registered Collection provides on/off control of a light or fixture from a single location, while combining clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately. |
| Long Description | The perfect upgrade for your basic light switch, the Single-Pole Switch from the radiant Registered Collection provides on/off control of a light or fixture from a single location, while combining clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately. |
| Product Type | Radiant Switch 1P 15A 120/277V Ni |
| Special Features | Everyone wants a home that's a step above ordinary. Now the radiant® collection of switches, outlets, dimmers and home automation controls by Legrand puts that stylish finishing touch affordably within reach. radiant gets rid of unsightly screws, delivering clean looks in a range of colors and metallic finishes. |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007021059 |
| Manufacturers Part Number | TM870-NICC10 |
| UPC | 785007021059 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Weight Per each | 0.1775 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Residential |
| environmental conditions | UL94 V2 |
| Mounting | BOX |
| Operating Temperature | Maximun continuous +115°C, minimum -40°C |
| standard | CULUS, UL, CSA Listed, UL Listed |