



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1220 Elm Street
75482-0000, TX Sulphur Springs
Phone: 903-885-0024
Fax: 903-885-0352



TM874GRY Decor Switch 3W 15A 120/277V W/GRD Gy

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | TM874GRY |
| Manufacturer | Pass & Seymour/Legrand |
| Description | For Your Largest or Most Open Spaces, A Radiant Registered 4-Way Switch Enables Control Of A Single Light or Fixture From Three or More Separate Locations (Working In Conjunction With 3-Way Switches). Perfect For Basements or Multi-Level Rooms. Part Of The Radiant Collection, It Features Clean Lines and Smooth Paddle Action For A Sophisticated Touch. Made Exclusively For Use With Screwless Wall Plates From The Radiant Registered Collection, Sold Separately. |
| Weight per unit | 0.2700 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|---------------------|--|
| actuator | Rocker switch |
| amperage rating | 15 |
| Contact Rating | 15 Amp, 120/125 VAC |
| indoor/outdoor | Indoor |
| Load Rating | 15 A @ 120 VAC |
| Load Type | CFL, Xenon, LED, Halogen, Universal, Fluorescent, Incandescent |
| Material | Thermoplastic |
| media | Yes |
| Mounting Type | Wall Box |
| Number of Gangs | 1.0 |
| Number of Switches | 1.0 |
| operating cycles | 50000 |
| Poles | 4-Way |
| Switch Type | Paddle |
| throw type | Single Throw |
| Voltage | 120 VAC, 125 VAC |
| Voltage Rating | 120 |
| Wall Plate Included | NO |
| Wire Size | #14 - #10 Awg |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | SATIN |
|--------|-------|

Dimensions and Weight

| | |
|------|--|
| Size | 1.27" Depth x 1.43" Width x 4.19" Height |
|------|--|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1220 Elm Street
75482-0000, TX Sulphur Springs
Phone: 903-885-0024
Fax: 903-885-0352

Descriptions

| | |
|------------------------|---|
| Description | DECOR SWITCH 3W 15A 120/277V W/GRD GY |
| extra long description | P&S TM874GRY DECOR SWITCH 3W 15A 12 |
| Features | Decorator Style |
| Long Description | For your largest or most open spaces, a radiant Registered 4-Way Switch enables control of a single light or fixture from three or more separate locations (working in conjunction with 3-Way Switches). Perfect for basements or multi-level rooms. Part of the radiant Collection, it features clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately. |
| Product Type | Decor Switch 3W 15A 120/277V W/GRD Gy |
| Special Features | Everyone wants a home that's a step above ordinary. Now the radiant® collection of switches, outlets, dimmers and home automation controls by Legrand puts that stylish finishing touch affordably within reach. radiant gets rid of unsightly screws, delivering clean looks in a range of colors and metallic finishes. |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007060508 |
| Manufacturers Part Number | TM874GRY |
| UPC | 785007060508 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.27 |

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Residential |
| environmental conditions | UL94 V2 |
| Mounting | BOX |
| Operating Temperature | Maximun continuous +115°C, minimum -40°C |
| standard | CULUS, CSA Listed, UL Listed |