



Pass and Seymour  
Combination Openings, 1 Toggle Switch and 1 Decorator, Two Gang, White  
Part No. TP126W



Trademaster Plate 2-Gang 1toggle 1 Decorator

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007275391
Country Of Origin	Mexico	Material	Nylon
Wall Plate Type	Combination, Decorator, Toggle Switch	Application Sector	Commercial, Residential
Standard	CSA, UL514	Warranty Type	Limited Lifetime Warranty
Type	Wall Plate		

### Dimensions

---

Product Width US	4.75 in	Product Depth US	0.25 in
------------------	---------	------------------	---------

---

Product Height US	4.6875 in
-------------------	-----------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

### Technical Information

---

Cutout	Toggle and Decorator	Thickness	0.07 in
--------	----------------------	-----------	---------

---

Number of Gangs	2	Indoor/Outdoor	Indoor
-----------------	---	----------------	--------

---

Orientation	Horizontal
-------------	------------

---



Pass and Seymour  
Combination Openings, 1 Toggle Switch and 1 Decorator, Two Gang, White  
Part No. TP126W



Trademaster Plate 2-Gang 1 toggle 1 Decorator

## Features & Benefits

Molded of rugged, practically indestructible self-extinguishing nylon. ('TP' series only.)

Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.

Nominal thickness, .070 inch.

Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Preferred for hospital, industrial, institutional, and other high-abuse applications.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007275391
Country Of Origin	Mexico	Material	Nylon
Wall Plate Type	Combination, Decorator, Toggle Switch	Application Sector	Commercial, Residential
Standard	CSA, UL514	Warranty Type	Limited Lifetime Warranty
Type	Wall Plate		

### Dimensions

---

Product Width US	4.75 in	Product Depth US	0.25 in
------------------	---------	------------------	---------

---

Product Height US	4.6875 in
-------------------	-----------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	143222	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

### Technical Information

---

Cutout	Toggle and Decorator	Thickness	0.07 in
--------	----------------------	-----------	---------

---

Number of Gangs	2	Indoor/Outdoor	Indoor
-----------------	---	----------------	--------

---

Orientation	Horizontal
-------------	------------

---