# Specifications



## Eaton TP217

Eaton Crouse-Hinds series Switch Box, (1) 1/2", Conduit (no clamps), 2-1/2", (1) 1/2", Steel, Ears, Gangable, 12.5 cubic inch capacity

| General specifications | |
|---|---|
| **PRODUCT NAME** | Eaton Crouse-Hinds series switch box |
| **CATALOG NUMBER** | TP217 |
| **UPC** | 786189102178 |
| **PRODUCT LENGTH/DEPTH** | 2 in |
| **PRODUCT HEIGHT** | 3 in |
| **PRODUCT WIDTH** | 2.5 in |
| **PRODUCT WEIGHT** | 0.64 lb |

Powering Business Worldwide

## Certifications and compliances

| | |
|---|---|
| **AREA CLASSIFICATION** | Ordinary/Non-Hazardous Locations |
| **STANDARDS TYPE** | NEC/CEC |

## Product specifications

| | |
|---|---|
| **DEPTH** | 2-1/2" |
| **TYPE** | Gangable |
| **CAPACITY** | 12.5 cubic in |
| **CONDUIT/CABLE** | Conduit (no clamps) |
| **END KNOCKOUTS** | (1) 1/2 in |
| **BOTTOM KNOCKOUTS** | (1) 1/2 in |
| **MATERIAL** | Steel |
| **SPECIAL FEATURES** | Ears |

## Resources

| | |
|---|---|
| CATALOGS | Crouse-Hinds series Steel Switch Boxes catalog page |
| CERTIFICATION REPORTS | Steel Switch Boxes UL certification<br>Steel Switch Boxes Canadian certification |
| SPECIFICATIONS AND DATASHEETS | Steel Outlet Boxes for Electrical Systems<br>Eaton Specification Sheet - TP217 |

| | |
|---|---|
| **PROJECT NAME:** | |
| **PROJECT NUMBER:** | |
| **PREPARED BY:** | |
| **DATE:** | |

**Eaton Corporation plc**
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.

# Specifications



## Eaton TP217

Eaton Crouse-Hinds series Switch Box, (1) 1/2", Conduit (no clamps), 2-1/2", (1) 1/2", Steel, Ears, Gangable, 12.5 cubic inch capacity

| General specifications | |
|---|---|
| **PRODUCT NAME** | Eaton Crouse-Hinds series switch box |
| **CATALOG NUMBER** | TP217 |
| **UPC** | 786189102178 |
| **PRODUCT LENGTH/DEPTH** | 2 in |
| **PRODUCT HEIGHT** | 3 in |
| **PRODUCT WIDTH** | 2.5 in |
| **PRODUCT WEIGHT** | 0.64 lb |

Powering Business Worldwide

## Certifications and compliances

| | |
|---|---|
| **AREA CLASSIFICATION** | Ordinary/Non-Hazardous Locations |
| **STANDARDS TYPE** | NEC/CEC |

## Product specifications

| | |
|---|---|
| **DEPTH** | 2-1/2" |
| **TYPE** | Gangable |
| **CAPACITY** | 12.5 cubic in |
| **CONDUIT/CABLE** | Conduit (no clamps) |
| **END KNOCKOUTS** | (1) 1/2 in |
| **BOTTOM KNOCKOUTS** | (1) 1/2 in |
| **MATERIAL** | Steel |
| **SPECIAL FEATURES** | Ears |

## Resources

| | |
|---|---|
| CATALOGS | Crouse-Hinds series Steel Switch Boxes catalog page |
| CERTIFICATION REPORTS | Steel Switch Boxes UL certification<br>Steel Switch Boxes Canadian certification |
| SPECIFICATIONS AND DATASHEETS | Steel Outlet Boxes for Electrical Systems<br>Eaton Specification Sheet - TP217 |

| | |
|---|---|
| **PROJECT NAME:** | |
| **PROJECT NUMBER:** | |
| **PREPARED BY:** | |
| **DATE:** | |

**Eaton Corporation plc**
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.