

Specifications



Eaton TP222

Eaton Crouse-Hinds series Switch Box, (1) 1/2", S, set 5/8", Conduit (no clamps), 2-1/2", (1) 1/2", Steel, (1) 1/2", 1 side, Gangable, 12.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series switch box
CATALOG NUMBER	TP222
UPC	786189102222
PRODUCT LENGTH/DEPTH	2 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	2.5 in
PRODUCT WEIGHT	0.65 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

DEPTH	2-1/2"
TYPE	Gangable
CAPACITY	12.5 cubic in
CONDUIT/CABLE	Conduit (no clamps)

BRACKET STYLE	S, Set 5/8"
END KNOCKOUTS	(1) 1/2 in
SIDE KNOCKOUTS	(1) 1/2 in, 1 side
BOTTOM KNOCKOUTS	(1) 1/2 in
MATERIAL	Steel

Resources

CATALOGS [Crouse-Hinds series Steel Switch Boxes catalog page](#)

CERTIFICATION REPORTS [Steel Switch Boxes Canadian certification](#)

[Steel Switch Boxes UL certification](#)

SPECIFICATIONS AND DATASHEETS [Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP222](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton TP222

Eaton Crouse-Hinds series Switch Box, (1) 1/2", S, set 5/8", Conduit (no clamps), 2-1/2", (1) 1/2", Steel, (1) 1/2", 1 side, Gangable, 12.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series switch box
CATALOG NUMBER	TP222
UPC	786189102222
PRODUCT LENGTH/DEPTH	2 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	2.5 in
PRODUCT WEIGHT	0.65 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

DEPTH	2-1/2"
TYPE	Gangable
CAPACITY	12.5 cubic in
CONDUIT/CABLE	Conduit (no clamps)

BRACKET STYLE	S, Set 5/8"
END KNOCKOUTS	(1) 1/2 in
SIDE KNOCKOUTS	(1) 1/2 in, 1 side
BOTTOM KNOCKOUTS	(1) 1/2 in
MATERIAL	Steel

Resources

CATALOGS [Crouse-Hinds series Steel Switch Boxes catalog page](#)

CERTIFICATION REPORTS [Steel Switch Boxes Canadian certification](#)

[Steel Switch Boxes UL certification](#)

SPECIFICATIONS AND DATASHEETS [Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP222](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

