

# Eaton TP256

Catalog Number: TP256

Eaton Crouse-Hinds series Octagon Outlet Box, (1) 1/2", 3-1/2", Conduit (no clamps), 1-1/2", Steel, (4) 1/2", Fixture rated, 9.0 cubic inch capacity

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series octagon outlet box	TP256
	UPC
	786189102567
<b>Product Length/Depth</b>	<b>Product Height</b>
3.25 in	1.5 in
<b>Product Width</b>	<b>Product Weight</b>
3.25 in	0.41 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

3-1/2"

### Depth

1-1/2"

### Capacity

9 cubic in

### Conduit/cable

Conduit (no clamps)

### Side knockouts

(4) 1/2 in

### Bottom Knockouts

(1) 1/2 in

### Material

Steel

### Special features

Fixture rated

## Resources

### Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

### Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP256](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton TP256

Catalog Number: TP256

Eaton Crouse-Hinds series Octagon Outlet Box, (1) 1/2", 3-1/2", Conduit (no clamps), 1-1/2", Steel, (4) 1/2", Fixture rated, 9.0 cubic inch capacity



## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series octagon outlet box	TP256
	UPC
	786189102567
Product Length/Depth	Product Height
3.25 in	1.5 in
Product Width	Product Weight
3.25 in	0.41 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

3-1/2"

### Depth

1-1/2"

### Capacity

9 cubic in

### Conduit/cable

Conduit (no clamps)

### Side knockouts

(4) 1/2 in

### Bottom Knockouts

(1) 1/2 in

### Material

Steel

### Special features

Fixture rated

## Resources

### Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

### Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP256](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)