

Eaton TP258

Catalog Number: TP258

Eaton Crouse-Hinds series Octagon Outlet Box, 3-1/4", Conduit (no clamps), 1-1/2", Steel, (4) 1/2", Fixture rated, Extension ring, 9.0 cubic inch capacity



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series octagon outlet box	TP258
	UPC
	786189102581
Product Length/Depth	Product Height
3.25 in	1.5 in
Product Width	Product Weight
3.25 in	0.31 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

3-1/4"

Depth

1-1/2"

Capacity

9 cubic in

Conduit/cable

Conduit (no clamps)

Side knockouts

(4) 1/2 in

Material

Steel

Type

Extension ring

Special features

Fixture rated

Resources

Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP258](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TP258

Catalog Number: TP258

Eaton Crouse-Hinds series Octagon Outlet Box, 3-1/4", Conduit (no clamps), 1-1/2", Steel, (4) 1/2", Fixture rated, Extension ring, 9.0 cubic inch capacity



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series octagon outlet box	TP258
	UPC
	786189102581
Product Length/Depth	Product Height
3.25 in	1.5 in
Product Width	Product Weight
3.25 in	0.31 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

3-1/4"

Depth

1-1/2"

Capacity

9 cubic in

Conduit/cable

Conduit (no clamps)

Side knockouts

(4) 1/2 in

Material

Steel

Type

Extension ring

Special features

Fixture rated

Resources

Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP258](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)