

Specifications



Eaton TP274

Eaton Crouse-Hinds series Octagon Outlet Box, (5) 1/2", 4", Conduit (no clamps), 1-1/2", Steel, (4) 1/2", Fixture rated, 15.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series octagon outlet box
CATALOG NUMBER	TP274
UPC	786189102741
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.5 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
DEPTH	1-1/2"
CAPACITY	15.5 cubic in
CONDUIT/CABLE	Conduit (no clamps)

SIDE KNOCKOUTS	(4) 1/2 in
BOTTOM KNOCKOUTS	(5) 1/2 in
MATERIAL	Steel
SPECIAL FEATURES	Fixture rated

Resources

CATALOGS

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

CERTIFICATION REPORTS

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP274](#)

[Steel Outlet Boxes for Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton TP274

Eaton Crouse-Hinds series Octagon Outlet Box, (5) 1/2", 4", Conduit (no clamps), 1-1/2", Steel, (4) 1/2", Fixture rated, 15.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series octagon outlet box
CATALOG NUMBER	TP274
UPC	786189102741
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.5 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
DEPTH	1-1/2"
CAPACITY	15.5 cubic in
CONDUIT/CABLE	Conduit (no clamps)

SIDE KNOCKOUTS	(4) 1/2 in
BOTTOM KNOCKOUTS	(5) 1/2 in
MATERIAL	Steel
SPECIAL FEATURES	Fixture rated

Resources

CATALOGS

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

CERTIFICATION REPORTS

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP274](#)

[Steel Outlet Boxes for Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

