

Eaton TP377

Catalog Number: TP377

Eaton Crouse-Hinds series Octagon Box and Adjustable Bar Set, 4", NM clamps, 1-1/2", Steel, Fixture rated, use with 4" octagon box, 16", 15.5 cubic inch capacity

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series octagon box and adjustable bar set	TP377
	UPC
	786189103779
Product Length/Depth	Product Height
16 in	1.5 in
Product Width	Product Weight
4 in	1.02 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4"

Depth

1-1/2"

Capacity

15.5 cubic in

Conduit/cable

NM clamps

Stud spacing

16"

Material

Steel

Special features

Fixture rated, use with 4" octagon box

Resources

Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP377](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TP377

Catalog Number: TP377

Eaton Crouse-Hinds series Octagon Box and Adjustable Bar Set, 4", NM clamps, 1-1/2", Steel, Fixture rated, use with 4" octagon box, 16", 15.5 cubic inch capacity

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series octagon box and adjustable bar set	TP377
	UPC
	786189103779
Product Length/Depth	Product Height
16 in	1.5 in
Product Width	Product Weight
4 in	1.02 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4"

Depth

1-1/2"

Capacity

15.5 cubic in

Conduit/cable

NM clamps

Stud spacing

16"

Material

Steel

Special features

Fixture rated, use with 4" octagon box

Resources

Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP377](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)