

# Eaton TP432RED

Catalog Number: TP432RED

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", Red, Conduit (no clamps), Welded, 2-1/8", Steel, (8) 3/4", 30.3 cubic inch capacity



## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series square outlet box	TP432RED
	UPC 662279005119
Product Length/Depth	Product Height
4 in	2.13 in
Product Width	Product Weight
4 in	0.9 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4"

### Capacity

30.3 cubic in

### Depth

2-1/8"

### Conduit/cable

Conduit (no clamps)

### Construction

Welded

### Side knockouts

(8) 3/4 in

### Bottom Knockouts

(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E

### Color

Red

### Material

Steel

## Resources

### Catalogs

[Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

### Certification reports

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP432RED](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton TP432RED

Catalog Number: TP432RED

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", Red, Conduit (no clamps), Welded, 2-1/8", Steel, (8) 3/4", 30.3 cubic inch capacity



## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series square outlet box	TP432RED
	UPC 662279005119
Product Length/Depth	Product Height
4 in	2.13 in
Product Width	Product Weight
4 in	0.9 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4"

### Capacity

30.3 cubic in

### Depth

2-1/8"

### Conduit/cable

Conduit (no clamps)

### Construction

Welded

### Side knockouts

(8) 3/4 in

### Bottom Knockouts

(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E

### Color

Red

### Material

Steel

## Resources

### Catalogs

[Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

### Certification reports

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP432RED](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)