

# Eaton TP504

Catalog Number: TP504

Eaton Crouse-Hinds series Square Surface Cover, 4", Raised surface, Steel, For one toggle switch and one single receptacle 1-13/32" diameter, 5.5 cubic inch capacity



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series square surface cover	TP504
	UPC
	786189105049
<b>Product Length/Depth</b>	<b>Product Height</b>
4 in	0.5 in
<b>Product Width</b>	<b>Product Weight</b>
4 in	0.31 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4"

### Capacity

5.5 cubic in

### Configuration

Raised surface

### Material

Steel

### Type

For one toggle switch and one single receptacle 1-13/32" diameter

## Resources

### Catalogs

[Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

### Certification reports

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP504](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.




[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton TP504

Catalog Number: TP504

Eaton Crouse-Hinds series Square Surface Cover, 4", Raised surface, Steel, For one toggle switch and one single receptacle 1-13/32" diameter, 5.5 cubic inch capacity



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series square surface cover	TP504
	UPC
	786189105049
<b>Product Length/Depth</b>	<b>Product Height</b>
4 in	0.5 in
<b>Product Width</b>	<b>Product Weight</b>
4 in	0.31 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Box size

4"

### Capacity

5.5 cubic in

### Configuration

Raised surface

### Material

Steel

### Type

For one toggle switch and one single receptacle 1-13/32" diameter

## Resources

### Catalogs

[Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

### Certification reports

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

### Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP504](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)