

Specifications



Eaton TP675

Eaton Crouse-Hinds series Masonry Box, (2) 1/2", (2) 3/4", 3-1/2", (2) 1/2", (2) 3/4", Steel, Single-gang, (4) 1/2", (4) 3/4", Gangable, 22.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series masonry box
CATALOG NUMBER	TP675
UPC	786189106756
PRODUCT LENGTH/DEPTH	3.75 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	1.94 in
PRODUCT WEIGHT	0.82 lb
PRODUCT TYPE	Masonry box



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

DEPTH	3-1/2"
NUMBER OF GANGS	Single-gang
END KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
SIDE KNOCKOUTS	(4) 1/2 in, (4) 3/4 in
BOTTOM KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
CAPACITY	22 cubic in
MATERIAL	Steel
TYPE	Gangable

Resources

CATALOGS	Crouse-Hinds series Steel Masonry Boxes catalog page
CERTIFICATION REPORTS	Steel Masonry Boxes Canadian certification Steel Masonry Boxes UL certification
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TP675 Steel Outlet Boxes for Electrical Systems

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Eaton TP675

Eaton Crouse-Hinds series Masonry Box, (2) 1/2", (2) 3/4", 3-1/2", (2) 1/2", (2) 3/4", Steel, Single-gang, (4) 1/2", (4) 3/4", Gangable, 22.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series masonry box
CATALOG NUMBER	TP675
UPC	786189106756
PRODUCT LENGTH/DEPTH	3.75 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	1.94 in
PRODUCT WEIGHT	0.82 lb
PRODUCT TYPE	Masonry box



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

DEPTH	3-1/2"
NUMBER OF GANGS	Single-gang
END KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
SIDE KNOCKOUTS	(4) 1/2 in, (4) 3/4 in
BOTTOM KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
CAPACITY	22 cubic in
MATERIAL	Steel
TYPE	Gangable

Resources

CATALOGS	Crouse-Hinds series Steel Masonry Boxes catalog page
CERTIFICATION REPORTS	Steel Masonry Boxes Canadian certification Steel Masonry Boxes UL certification
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TP675 Steel Outlet Boxes for Electrical Systems

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

