# Specifications



## Eaton TP691

Eaton Crouse-Hinds series Masonry Box, (4) 1/2", (4) 3/4", 3-1/2", (4) 1/2", (4) 3/4", Steel, Two-gang, (2) 1/2", (2) 3/4", 44.0 cubic inch capacity

### General specifications

| | |
|---|---|
| **PRODUCT NAME** | Eaton Crouse-Hinds series masonry box |
| **CATALOG NUMBER** | TP691 |
| **UPC** | 786189106916 |
| **PRODUCT LENGTH/DEPTH** | 3.75 in |
| **PRODUCT HEIGHT** | 3.75 in |
| **PRODUCT WIDTH** | 3.75 in |
| **PRODUCT WEIGHT** | 1.2 lb |

## Certifications and compliances

| | |
|---|---|
| **AREA CLASSIFICATION** | Ordinary/Non-Hazardous Locations |
| **STANDARDS TYPE** | NEC/CEC |

## Product specifications

| | |
|---|---|
| **DEPTH** | 3-1/2" |
| **NUMBER OF GANGS** | Two-gang |
| **END KNOCKOUTS** | (4) 1/2 in, (4) 3/4 in |
| **SIDE KNOCKOUTS** | (2) 1/2 in, (2) 3/4 in |
| **BOTTOM KNOCKOUTS** | (4) 1/2 in, (4) 3/4 in |
| **CAPACITY** | 44 cubic in |
| **MATERIAL** | Steel |

## Resources

| | |
|---|---|
| CATALOGS | Crouse-Hinds series Steel Masonry Boxes catalog page |
| CERTIFICATION REPORTS | Steel Masonry Boxes UL certification<br>Steel Masonry Boxes Canadian certification |
| SPECIFICATIONS AND DATASHEETS | Steel Outlet Boxes for Electrical Systems<br>Eaton Specification Sheet - TP691 |

| | |
|---|---|
| **PROJECT NAME:** | |
| **PROJECT NUMBER:** | |
| **PREPARED BY:** | |
| **DATE:** | |

**Eaton Corporation plc**
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.

# Specifications



## Eaton TP691

Eaton Crouse-Hinds series Masonry Box, (4) 1/2", (4) 3/4", 3-1/2", (4) 1/2", (4) 3/4", Steel, Two-gang, (2) 1/2", (2) 3/4", 44.0 cubic inch capacity

### General specifications

| | |
|---|---|
| **PRODUCT NAME** | Eaton Crouse-Hinds series masonry box |
| **CATALOG NUMBER** | TP691 |
| **UPC** | 786189106916 |
| **PRODUCT LENGTH/DEPTH** | 3.75 in |
| **PRODUCT HEIGHT** | 3.75 in |
| **PRODUCT WIDTH** | 3.75 in |
| **PRODUCT WEIGHT** | 1.2 lb |

## Certifications and compliances

| | |
|---|---|
| **AREA CLASSIFICATION** | Ordinary/Non-Hazardous Locations |
| **STANDARDS TYPE** | NEC/CEC |

## Product specifications

| | |
|---|---|
| **DEPTH** | 3-1/2" |
| **NUMBER OF GANGS** | Two-gang |
| **END KNOCKOUTS** | (4) 1/2 in, (4) 3/4 in |
| **SIDE KNOCKOUTS** | (2) 1/2 in, (2) 3/4 in |
| **BOTTOM KNOCKOUTS** | (4) 1/2 in, (4) 3/4 in |
| **CAPACITY** | 44 cubic in |
| **MATERIAL** | Steel |

## Resources

| | |
|---|---|
| CATALOGS | Crouse-Hinds series Steel Masonry Boxes catalog page |
| CERTIFICATION REPORTS | Steel Masonry Boxes UL certification<br>Steel Masonry Boxes Canadian certification |
| SPECIFICATIONS AND DATASHEETS | Steel Outlet Boxes for Electrical Systems<br>Eaton Specification Sheet - TP691 |

| | |
|---|---|
| **PROJECT NAME:** | |
| **PROJECT NUMBER:** | |
| **PREPARED BY:** | |
| **DATE:** | |

**Eaton Corporation plc**
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.