

# Specifications



Photo is representative

## Eaton TP730

Eaton Crouse-Hinds series Square Surface Cover, 4-11/16", Raised surface, Steel, For one 20 amp single receptacle 1.620" diameter, 9.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series square surface cover
<b>CATALOG NUMBER</b>	TP730
<b>UPC</b>	786189107302
<b>PRODUCT LENGTH/DEPTH</b>	4.69 in
<b>PRODUCT HEIGHT</b>	0.06 in
<b>PRODUCT WIDTH</b>	4.69 in
<b>PRODUCT WEIGHT</b>	0.5 lb



### Certifications and compliances

**AREA CLASSIFICATION** Ordinary/Non-Hazardous

### Product specifications

**BOX SIZE** 4-11/16"

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC

<b>CAPACITY</b>	9 cubic in
<b>CONFIGURATION</b>	Raised surface
<b>MATERIAL</b>	Steel
<b>TYPE</b>	For one 20 amp single receptacle 1.620" diameter

## Resources

### 3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds TP730 3D drawing](#)

### CATALOGS

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

### CERTIFICATION REPORTS

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP730](#)

[Steel Outlet Boxes for Electrical Systems](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative

## Eaton TP730

Eaton Crouse-Hinds series Square Surface Cover, 4-11/16", Raised surface, Steel, For one 20 amp single receptacle 1.620" diameter, 9.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series square surface cover
<b>CATALOG NUMBER</b>	TP730
<b>UPC</b>	786189107302
<b>PRODUCT LENGTH/DEPTH</b>	4.69 in
<b>PRODUCT HEIGHT</b>	0.06 in
<b>PRODUCT WIDTH</b>	4.69 in
<b>PRODUCT WEIGHT</b>	0.5 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous
----------------------------	------------------------

### Product specifications

<b>BOX SIZE</b>	4-11/16"
-----------------	----------

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC

<b>CAPACITY</b>	9 cubic in
<b>CONFIGURATION</b>	Raised surface
<b>MATERIAL</b>	Steel
<b>TYPE</b>	For one 20 amp single receptacle 1.620" diameter

## Resources

### 3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds TP730 3D drawing](#)

### CATALOGS

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

### CERTIFICATION REPORTS

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP730](#)

[Steel Outlet Boxes for Electrical Systems](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

