



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TY27M2 13" Nylon Red Cable Tie

Abb Installation Products, Inc

Catalog Number	TY27M2
Manufacturer	Abb Installation Products, Inc
Description	High Performance Cable Tie, Red Color Nylon 6.6, Length Of 343MM (13.5 Inches) For Bundle Diameter Up to 102MM (4 Inches), Width Of 6.9MM (0.27 Inch), Tensile Strength Rating Of 534 Newtons (120 Pounds), Operating Temperature Of -20 Degrees Celsius (-4 F) to 85 Degrees Celsius (185 F)
Weight per unit	0.0150 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Tensile Strength	120
------------------	-----

Dimensions and Weight

Length	13.5
Thickness	0.06
Width	0.27

Descriptions

Description	13" NYLON RED CABLE TIE
extra long description	ABB TY27M-2 CABLE TIE 120LB 13IN RE
Long Description	High Performance Cable Tie, Red Color Nylon 6.6, Length of 343mm (13.5 Inches) for Bundle Diameter up to 102mm (4 Inches), Width of 6.9mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -20 Degrees Celsius (-4 F) to 85 Degrees Celsius (185 F)
Product Type	Cable Tie 120LB 13IN Red Nylon
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210845005
Manufacturers Part Number	TY27M-2
UPC	786210845005

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HIGH PERFORMANCE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	500
Package	1000
Weight Per each	0.015

Uses, Certifications, and Standards

standard	UL E49405
----------	-----------