



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TY528MX 14.19" Uv Rated "Ty-Rap" Cable Tie

Abb Installation Products, Inc

Catalog Number	TY528MX
Manufacturer	Abb Installation Products, Inc
Description	Cable Tie, Black Polyamide (Nylon 6.6) For Temperatures Up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant For Indoor and Outdoor Applications, Length Of 360.68MM (14.2 Inches), Width Of 4.83MM (0.19 Inches), Tensile Strength Rating Of 222 Newtons (50 Pounds)
Weight per unit	0.0070 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Tensile Strength	50
------------------	----

Dimensions and Weight

Length	14.2
Thickness	0.05
Width	0.19

Descriptions

Description	14.19" UV RATED "TY-RAP" CABLE TIE
extra long description	ABB TY528MX CBL TIE 50LB 14.2PO UV
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 360.68mm (14.2 Inches), Width of 4.83mm (0.19 Inches), Tensile Strength Rating of 222 Newtons (50 pounds)
Product Type	CBL Tie 50LB 14.2PO Uv Black
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210805146
Manufacturers Part Number	TY528MX
UPC	786210805146

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HIGH PERFORMANCE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
--------	-----

Package	500
---------	-----

Weight Per each	0.007
-----------------	-------