

Specifications

Eaton U27

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 3/4"



Photo is representative

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	U27
UPC	662276465787
PRODUCT LENGTH/DEPTH	7.5 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	1.69 in
PRODUCT WEIGHT	1.7 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

SHAPE U

	Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	3 4 12

TRADE SIZE	3/4"
MATERIAL	Feraloy iron alloy

Resources

3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds U27 3D drawing](#)

CATALOGS

[Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

INSTALLATION INSTRUCTIONS

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - U27](#)

TECHNICAL SERVICE BULLETINS

[Industrial Fittings Wire Fill Chart](#)

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications

Eaton U27

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 3/4"



Photo is representative

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	U27
UPC	662276465787
PRODUCT LENGTH/DEPTH	7.5 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	1.69 in
PRODUCT WEIGHT	1.7 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

SHAPE U

	Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	3 4 12

TRADE SIZE	3/4"
MATERIAL	Feraloy iron alloy

Resources

3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds U27 3D drawing](#)

CATALOGS

[Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

INSTALLATION INSTRUCTIONS

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - U27](#)

TECHNICAL SERVICE BULLETINS

[Industrial Fittings Wire Fill Chart](#)

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

