

# Specifications

## Eaton U37

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 1"



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	U37
<b>UPC</b>	662276465794
<b>PRODUCT LENGTH/DEPTH</b>	9.69 in
<b>PRODUCT HEIGHT</b>	4.81 in
<b>PRODUCT WIDTH</b>	2 in
<b>PRODUCT WEIGHT</b>	2.65 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	3

### Product specifications

<b>SHAPE</b>	U
<b>TRADE SIZE</b>	1"
<b>MATERIAL</b>	Feraloy iron alloy

## Resources

**3D CAD DRAWING PACKAGE** [Eaton Crouse-Hinds U37 3D drawing](#)

**CATALOGS** [Crouse-Hinds series Form 7 catalog page](#)

**CERTIFICATION REPORTS** [Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

**INSTALLATION INSTRUCTIONS** [IF 863 - Conduit Body Wire Pulling](#)  
[IF 964 - Conduit Body Wire Pulling](#)

**SPECIFICATIONS AND DATASHEETS** [Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - U37](#)

**TECHNICAL SERVICE BULLETINS** [Industrial Fittings Bend Radius and Cubic Capacity Chart](#)  
[Industrial Fittings Wire Fill Chart](#)

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications

## Eaton U37

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 1"



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	U37
<b>UPC</b>	662276465794
<b>PRODUCT LENGTH/DEPTH</b>	9.69 in
<b>PRODUCT HEIGHT</b>	4.81 in
<b>PRODUCT WIDTH</b>	2 in
<b>PRODUCT WEIGHT</b>	2.65 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	3

### Product specifications

<b>SHAPE</b>	U
<b>TRADE SIZE</b>	1"
<b>MATERIAL</b>	Feraloy iron alloy

## Resources

**3D CAD DRAWING PACKAGE** [Eaton Crouse-Hinds U37 3D drawing](#)

**CATALOGS** [Crouse-Hinds series Form 7 catalog page](#)

**CERTIFICATION REPORTS** [Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

**INSTALLATION INSTRUCTIONS** [IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

**SPECIFICATIONS AND DATASHEETS** [Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - U37](#)

**TECHNICAL SERVICE BULLETINS** [Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

