

Specifications

Eaton U67

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 2"



Photo is representative

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	U67
UPC	662276465831
PRODUCT LENGTH/DEPTH	17.31 in
PRODUCT HEIGHT	8.63 in
PRODUCT WIDTH	3.63 in
PRODUCT WEIGHT	8.85 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
----------------------------	------------------------

Product specifications

SHAPE	U
--------------	---

	Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	3 4 12

TRADE SIZE	2"
MATERIAL	Feraloy iron alloy

Resources

3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds U67 3D drawing](#)

CATALOGS

[Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

INSTALLATION INSTRUCTIONS

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - U67](#)

TECHNICAL SERVICE BULLETINS

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications

Eaton U67

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, U shape, 2"



Photo is representative

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	U67
UPC	662276465831
PRODUCT LENGTH/DEPTH	17.31 in
PRODUCT HEIGHT	8.63 in
PRODUCT WIDTH	3.63 in
PRODUCT WEIGHT	8.85 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
----------------------------	------------------------

Product specifications

SHAPE	U
--------------	---

	Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	3 4 12

TRADE SIZE	2"
MATERIAL	Feraloy iron alloy

Resources

3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds U67 3D drawing](#)

CATALOGS

[Crouse-Hinds series Form 7 catalog page](#)

CERTIFICATION REPORTS

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

INSTALLATION INSTRUCTIONS

[IF 863 - Conduit Body Wire Pulling](#)

[IF 964 - Conduit Body Wire Pulling](#)

SPECIFICATIONS AND DATASHEETS

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - U67](#)

TECHNICAL SERVICE BULLETINS

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

