



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## UAG12500 1/2" Ua Sealtite Conduit, Bonded UI 500' *Southwire Company*

Catalog Number	UAG12500
Manufacturer	Southwire Company
Description	UI Liquid-Tuff™ Liquidtight Conduit, Type LFMC, 6200 Series, Liquidtight Flexible Metal Conduit. Hot Dipped Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 1/2 Inch Diameter, 500 Foot Reel
Weight per unit	0.3000 (lbs/each)
Product Category	Flexible Metallic Conduit

### Features

Inside Diameter	0.622/0.642
Material	Steel
outside diameter	0.820/0.840

### Material, Color, and Finish

Color	Gray
Finish	PVC
Jacket Material	PVC

### Dimensions and Weight

Length	500
--------	-----

### Descriptions

Description	1/2" UA SEALTITE CONDUIT, BONDED UL 500'
extra long description	AFC 6202-45-00 1/2" UL LT LFMC GRA
Features	UL LIQUIDTUFF™ Liquidtight Flexible Steel Conduit designed for use as a raceway for power, control and communication cables in accordance with Article 350 of the National Electrical Code.
Long Description	UL LIQUID-TUFF™ Liquidtight Conduit, Type LFMC, 6200 Series, Liquidtight Flexible Metal Conduit. Hot Dipped Galvanized Low Carbon Steel, Flame Retardant PVC Jacket. Color: Gray, 1/2 inch Diameter, 500 Foot Reel
Product Type	1/2" UI LT LFMC Gray 500' RL
Short Description	1/2" UL LT LFMC GRAY 500' RL
Special Features	UL bonded strip 3/8in - 1.25in for grounding. UL Liquidtight all sizes. Sunlight resistant. Flame retardant PVD jacket. Hot dipped zinc galvanized steel low carbon steel core.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680119988
Manufacturers Part Number	55082605
UPC	077680119988

## Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	Liquidtight Flexible Metal Conduit

## Trade Size

Trade Size	1/2
------------	-----

## Packaging

Carton	500
Weight	0.31
Weight Per each	0.3

## Uses, Certifications, and Standards

Application	For Service Entrance Wiring Upto 6 FT
Temperature Rating	176