



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UAG4 4" Ua Sealtite Conduit, Bonded UL 25' *Southwire Company*

Catalog Number	UAG4
Manufacturer	Southwire Company
Description	TITAN2 Type UL LFMC Is Manufactured With A Spiral Wound Strip Of Heavy Gauge Corrosion-Resistant Hot-Dipped Galvanized Steel. For 3/8" Through 1-1/4" Trade Sizes The Core Is Constructed With A Square Locked Steel Strip With An Integral Copperbonding Strip Enclosed Within The Steel Convolutions. For 1-1/2" Through 4" Trade Sizes The Core Is Constructed With A Fully Interlocked Steel Strip. A Rugged Flame Retardant Flexible PVC Jacket Is Extruded Over The Steel Core. The Grey Jacket Resists Oils Mild
Weight per unit	3.1 (lbs/each)
Product Category	Conduit & Raceways

Features

outside diameter	4480
------------------	------

Dimensions and Weight

Length	25
--------	----

Descriptions

Description	4" UA SEALTITE CONDUIT, BONDED UL 25'
extra long description	SWC 55106704 Titan2 Type UL Liquidt
Long Description	Titan2 Type UL LFMC is manufactured with a spiral wound strip of heavy gauge corrosion-resistant hot-dipped galvanized steel. For 3/8" through 1-1/4" trade sizes the core is constructed with a square locked steel strip with an integral copperbonding strip enclosed within the steel convolutions. For 1-1/2" through 4" trade sizes the core is constructed with a fully interlocked steel strip. A rugged flame retardant flexible PVC jacket is extruded over the steel core. The grey jacket resists oils mild
Product Type	TITAN2 Type UL Liquidtight Flexible Metal Conduit

Manufacturer Information

Brand	Flexible Conduit
GTIN	00032886053443
Manufacturers Part Number	55106704
UPC	032886053443

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	LTM-UL



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Trade Size 4

Packaging

Carton 25

Weight Per each 3.1