

# Eaton UATH7330UFLCH

Catalog Number: UATH7330UFLCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, Large hub cover plate hub mounted, 7-jaw, 3-ph, 3/8 inch stud, Lever bypass, Gnd conn (#14-#2 Cu), Al, Triplex, Side-wired, 3-wire, Ringless, 600 Vac



## General specifications

### Product Name

Eaton meter socket

### Catalog Number

UATH7330UFLCH

### UPC

782116168941

### Product Length/Depth

6.5 in

### Product Height

39.88 in

### Product Width

20 in

### Product Weight

40 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Product specifications

### Type

Single-position commercial or residential service

### Amperage Rating

320A

### Feed type

Top/bottom

### Number of jaws

Seven-jaw

### Phase

Three-phase

### Utility approvals

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

FL : Tallahassee City Electric

### Line

3/8 in stud

### Load

3/8 in stud

### Enclosure material

Aluminum

### Number of wires

Three-wire

### Hub type

5 x 5 hub cover plate

### Connection

Ground connection

### Security

## Resources

### Catalogs

Residential and Light Commercial, Metering Products, Volume 1 Tab 4

### Specifications and datasheets

Eaton Specification Sheet - UATH7330UFLCH

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton UATH7330UFLCH

Catalog Number: UATH7330UFLCH

Eaton meter socket, 1-pos commercial or resi service, 320A, Over/under, Large hub cover plate hub mounted, 7-jaw, 3-ph, 3/8 inch stud, Lever bypass, Gnd conn (#14-#2 Cu), Al, Triplex, Side-wired, 3-wire, Ringless, 600 Vac



## General specifications

### Product Name

Eaton meter socket

### Catalog Number

UATH7330UFLCH

### UPC

782116168941

### Product Length/Depth

6.5 in

### Product Height

39.88 in

### Product Width

20 in

### Product Weight

40 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Product specifications

### Type

Single-position commercial or residential service

### Amperage Rating

320A

### Feed type

Top/bottom

### Number of jaws

Seven-jaw

### Phase

Three-phase

### Utility approvals

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

FL : Tallahassee City Electric

### Line

3/8 in stud

### Load

3/8 in stud

### Enclosure material

Aluminum

### Number of wires

Three-wire

### Hub type

5 x 5 hub cover plate

### Connection

Ground connection

### Security

## Resources

### Catalogs

Residential and Light Commercial, Metering Products, Volume 1 Tab 4

### Specifications and datasheets

Eaton Specification Sheet - UATH7330UFLCH

Ringless

Voltage rating

600 V

Bypass

Lever

Number of sockets

1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)