

Specifications



Photo is representative

Eaton UAT2R2332UFLCH

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, #6-350 kcmil, 4-jaw, 1-phase, #8-250 kcmil, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	UAT2R2332UFLCH
UPC	782116997817
PRODUCT LENGTH/DEPTH	5.38 in
PRODUCT HEIGHT	14.13 in
PRODUCT WIDTH	24.31 in
PRODUCT WEIGHT	29 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	Multiple position residential service
AMPERAGE RATING	200A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
ENCLOSURE	063 aluminum
UTILITY APPROVALS	FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
	IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
	KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
	NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
	OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
	SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)
	FL : Tallahassee City Electric
LINE	#6-350 kcmil
LOAD	#8-250 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	Hub cover plate
CONNECTION	Ground connection
SECURITY	Ringless
VOLTAGE RATING	600 V
NUMBER OF SOCKETS	2

Resources

CATALOGS

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - UAT2R2332UFLCH](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

